

#### FRAUNHOFER-INSTITUT FÜR BIOMEDIZINISCHE TECHNIK IBMT



- 1 Transmit-Receive Module connected to a Notebook (USB).
- 2 Liner Thickness Measurement with TRM.

# Fraunhofer Institute for Biomedical Engineering IBMT

Prof. Dr. Heiko Zimmermann Prof. Dr. Günter R. Fuhr Joseph-von-Fraunhofer-Weg 1 66280 Sulzbach Germany

## Contact

Peter K. Weber Ultrasound Systems Development Phone +49 6894 980-227 peter.weber@ibmt.fraunhofer.de

www.ibmt.fraunhofer.de

# TRANSMIT-RECEIVE MODULE (TRM)

#### **System Description**


High sampling rates and fast detection times as well as a flexible real-time signal evaluation are the requirements for ultrasonic measurements in real time. TRM is a DSP based single channel ultrasonic measuring system for pulse-echo-operation. The received signals are amplified, digitized and processed with a digital signal processor (DSP).

Typical applications for TRM are ultrasound based level metering, flow measurement, volume and distance metering or material characterization. It is used in many different fields like production lines, power and sewage plants, automotive sensing, environmental control or sonar applications.

#### **Application**

Ultrasound based flow and level metering as well as quantitative turbidity detection are flexible and reliable methods for process control in small and big facilities like hydroelectric power plants, sewage plants or production lines. Ultrasound is used for water and gas metering in homes as well as for level metering in tanks or vessels. The detection of flaws or the measurement of the thickness of liners are typical tasks in the quality control of sewer or fresh water pipes. Beyond the long term inspection of working facilities the technology is used for the final acceptance of new or reconstructed systems.





#### **Further Applications**

The 100%-control of manufacturing tolerances of parts or the quality control of laser lenses under operation conditions can be done by the use of appropriate sensors in combination with a fast and powerful hardware like the single channel systems TRM or USS. An integration of these systems in existing quality management systems is possible.

Further applications for ultrasonic based quality control are material characterizations, the measurement of temperatures, the detection of concentrations, bubble detection, the measurement of the thickness of layers or films, viscosity control or containments in liquids, e.g. in milk, yogurt or liquid chocolate.

#### **Specifications**

#### Transmitter

Frequency 0 - 25 MHzOutput Voltage  $\max 90 \text{ Vpp } (50 \Omega)$ Memory  $1 \text{ k} - 256 \text{ k} \times 18 \text{ bit}$ Waveform bidirectional Waveshape programmable

#### Receiver

input Impedance adjustable min. Input Voltage 20  $\mu$ Vpp Amplifiermax 100 dB Bandwidth 40 MHz Standard Filter adjustable

#### **DSP**

Signal Processor 56311 (150 MHz)
Program RAM 32 k x 24 bit
x-Data RAM 48 k x 24 bit
y-data RAM 48 k x 24 bit

#### Conversion

ADC 12 bit 100 MSPs Memory 1 k – 256 k x 18 bit

### **Power Consumption**


5V: 600 mA; 12 V: 100 mA

#### Multiplexer

up to 8 channels

#### Interfaces

ISA (internal PC)
serial RS 232
CAN (V 2.0B)
GP-IO
I2C
USB (with RS232 adaptor)
Trigger in and out
Stand Alone with external Power



- 1 Flow-Metering in a Hydroelectric
- 2 Wall Thickness Measurement.